


FOR THE DOOR INSTALLATION
PLEASE CONSULT THE
INSTALLATION MANUAL

PROTECTION OF THE
COMPARTMENT: NORM
UNI-EN-ISO-13857:2008
FOR PROTECTION WITH
METALLIC GRID, USE
A COMPACT MESH 12x12mm


TECHNICAL AREA
AT FLOOR "0"



PREPARE CORRUGATED
TUBE Ø10cm TO THE
TECHNICAL AREA

MAX DISTANCE
FROM GOODSLIFT TO
TECHNICAL AREA 4MT
(L. standard tube = 6 mt)


WALL IN CONCRETE CLASS 20/25
Standard fixing: Anchor mod. Fischer FBN II 12x50 (12x146)



TECHNICAL AREA


PREPARE CORRUGATED TUBE
Ø10cm TO THE TECHNICAL AREA

PREPARE TUBULAR 100x30 FLUSH
WITH THE GOODSLIFT ROOM
Only for standard door application



NOTE:
THRESHOLD ADAPTATION
BY CUSTOMER

MARK THE ENTRANCES AND THE HEIGHT OF FLOOR



MODEL: UP3 - 300Kg UP6 - 600Kg

Date: _____

Signature for approval: _____




MISURE IN mm

STROKE AND FLATBED DIMENSION			
MODEL	WIDTH (mm)	DEPTH (mm)	STROKE MAX (mm)
UP 3	1700	1300	7000
UP 6	1700	1300	7000

Motore	Tensione funzionamento	Avviamento	Interruttore consigliato*	Corrente nominale	Corrente avviamento
1,5kW	220 V - monofase	Diretto	2x16A id=0,3A	9,5	28
2,2kW	220 V - monofase	Diretto	2x16A id=0,3A	10,5	32

PREPARE POWER PH+T+N SWITCH AUTOMATIC MAGNETOTHERMIC WITH DIFFERENTIAL CURVE "C", Id = 0.3A



directlifts 1300 240 298 | info@directlifts.com.au | www.directlifts.com.au

Q.TA DESCRIZIONE: MODEL: UP3 - 300Kg UP6 - 600Kg STROKE MAX: 7000mm ONLY FOR GOODS

Cliente: _____ Disegno n°: TAV-UP36-STD01

Sostituito da: _____ Sostituisce il: _____